

BUFFER TANK SCHEDULE											
TANK NO.	APPLICATION	LOCATION	TANK TYPE	VOLUME (L)	MAX. PRESS (kPa)	MAX. TEMP (deg-C)	TANK. HEIGHT (mm)	TANK. DIA (mm)	CONN. SIZE (mm)	SHIPPING WEIGHT (Kg)	SPECIFICATION SECTION
BT-1	HYDONRIC BUFFER	GARAGE	2-PORT WELDED	750	875	115	1550	750	50.8	215	23-21-16

DUCTED HEATING COIL SCHEDULE												
			AIRSIDE DATA				WATER DATA					
UNIT NO.	APPLICATION	LOCATION	AIRFLOW (L/S)	P.D. (Pa)	EAT (deg-C)	LAT (deg-C)	EWT (deg-C)	LWT (deg-C)	FLOW (L/S)	P.D. (kPa)	HEAT CAPACITY (kW)	SPECIFICATION SECTION
HC-1	OFFICE HEATING	BOILER ROOM	650	30	18	35	80	70	0.33	35	14.0	23-36-00

DOMESTIC HOT WATER HEATER SCHEDULE								
UNIT NO.	APPLICATION	LOCATION	CONFIGURATION	RECOVERY RATE 50C TEMP RISE (LPH)	DHW VOLUME (L)	POWER (V/ph/Hz)	HEATING CAPACITY (kW)	SPECIFICATION SECTION
DWH-1	DHW SUPPLY	GARAGE	HYDRONIC INDIRECT	400	100	N/A	N/A	22-33-16
DWH-2	DHW BACKUP	GARAGE	ELECTRIC	25	23	120/1/60	2.0	22-33-16