



RETURN BIDS TO:

RETOURNER LES SOUMISSIONS À:

Travaux publics et Services gouvernementaux
Canada

Voir dans le document/

See herein

NA

Québec

NA

**SOLICITATION AMENDMENT
MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address

Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution

Travaux publics et Services gouvernementaux Canada
Place Bonaventure, portail Sud-Oue
800, rue de La Gauchetière Ouest
7^e étage, suite 7300
Montréal
Québec
H5A 1L6

Title - Sujet Numerical Vertical Milling Machine Numerical Vertical Milling Machine	
Solicitation No. - N° de l'invitation W7701-227437/B	Amendment No. - N° modif. 004
Client Reference No. - N° de référence du client W7701-227437	Date 2021-10-29
GETS Reference No. - N° de référence de SEAG PW-SMTA-030-16291	
File No. - N° de dossier MTA-1-44077 (030)	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM Eastern Standard Time EST on - le 2021-11-08 Heure Normale du l'Est HNE	
F.O.B. - F.A.B. Specified Herein - Précisé dans les présentes Plant-Usine: <input type="checkbox"/> Destination: <input type="checkbox"/> Other-Autre: <input checked="" type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Thérien, Renée-Ann	Buyer Id - Id de l'acheteur mta030
Telephone No. - N° de téléphone (514) 703-4947 ()	FAX No. - N° de FAX () -
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

AMENDMENT 004

This amendment is raised to post QUESTIONS - ANSWERS regarding this request and to update the following sections of the solicitation document (1.7, 2.5, 4.6 and 5.8 of the "Requirement Annex).

Please take note of the QUESTION & ANSWER regarding this request:

Question 1 : In reference to item 1.7 of annex "requirement" do you accept 4000mm (157") x 2700mm (106") as responsive to this requirement?

Answer : Yes.

Question 2 : In reference to item 2.5 of annex "requirement" do you accept maximum torque of 200 Nm as responsive to the requirement?

Answer : Yes.

Question 3 : In reference to item 4.6 of annex "requirement" do you accept 335 liters capacity?

Answer : Yes.

Question 4 : In reference to item 5.8 of annex "requirement" do you accept 7 seconds or less for chip-to-chip tool changing speed?

Answer : Yes.

Please take note of the update of the following sections of the solicitation document (1.7, 2.5, 4.6 and 5.8 of the annex "Requirement"

DELETE:

Item 1.7 of annex "Requirement"

- 1.7** The machine must have a footprint of a minimum 100 "X 100" (2540 X 2540 mm mm) in order to be considered an industrial machine and a maximum of 150 "X 150" (3810 mm X 3810 mm) to respect our available floor space.

Item 2.5 of annex "Requirement" and annex "Mandatory Technical Criteria"

2.5 Spindle 150 FT - LBS (203 NM) or more maximum torque;

Item 4.6 of annex "Requirement"

4.6 Coolant tank capacity: 92.5 gallons imp (350 litres) or more;

Item 5.8 of annex "Requirement"

5.8 Chip-to-chip tool changing speed: 6 seconds or less;

INSERT:

Item 1.7 of annex "Requirement"

1.7 The machine must have a footprint of a minimum 100 "X 100" (2540 X 2540 mm mm) in order to be considered an industrial machine and a maximum of 157 "X 157" (3987 mm X 3987 mm) to respect our available floor space.

Item 2.5 of annex "Requirement" and annex "Mandatory Technical Criteria"

2.5 Spindle 147.5 FT - LBS (200 NM) or more maximum torque;

Item 4.6 of annex "Requirement"

4.6 Coolant tank capacity: 74 gallons imp (335 litres) or more;

Item 5.8 of annex "Requirement"

5.8 Chip-to-chip tool changing speed: 7 seconds or less;

ALL OTHER TERMS AND CONDITIONS REMAIN THE SAME.