



## REQUEST FOR PROPOSAL AMENDMENT NO. 001

**Request for Proposal Amendment no. 001 is raised to provide questions and answers and to make modifications.**

**Question 1:** At A1.5 “Must have a minimum of 4 drawers to hold additional paper roles of various sizes.” Please confirm this requirement should read 4 roll capacity, and not 4 drawers.

**Answer 1:** Correct, please see Modifications 1 & 2.

**Question 2:** At A1.11 “Scanner must capable of scanning drawings up to 38” wide up to 900 dpi” Please confirm this requirement is a minimum of 38” wide scanning capabilities with a minimum resolution of 600 dpi

**Answer 2:** The scanner must have the capability to scan various document sizes up to a maximum of 38” wide with a minimum capability of 600 dpi. Please see Modifications 3 & 4.

**Question 3:** At A1.12 “Scanner must be capable of scanning large drawings up to 42”x 72” from Color, B&W, Dark originals, Photo Maps, red line drawings, and older cad drawings.” Please confirm this requirement states “up to 42”x 72” in error. Reference A1.11 requirement is scanning width requirement of 38”

**Answer 3:** That is an error and has been corrected. Please see Modification 5 & 6.

**Question 4:** Is there current equipment in place that needs to be removed and/or discarded? Confirm that the new device will be placed in existing device location.

**Answer 4:** There is an existing device, and Canada will be responsible for the removal and disposal of the existing equipment prior to install of the new device.

### Modification 1: At ANNEX A STATEMENT OF REQUIREMENT:

#### Delete:

<b>A1.5</b>	Must have a minimum of 4 drawers to hold additional paper roles of various sizes.
-------------	---

#### Insert:

<b>A1.5</b>	Must have a minimum of 4 roll capacity to hold additional paper rolls of various sizes.
-------------	---

**Modification 2: At ATTACHMENT 4.1 SUBSTANTIATION OF TECHNICAL COMPLIANCE FORM:**

**Delete:**

<b>A1.5</b>	Must have a minimum of 4 drawers to hold additional paper roles of various sizes.	Y/N		
-------------	---	-----	--	--

**Insert:**

<b>A1.5</b>	Must have a minimum of 4 roll capacity to hold additional paper rolls of various sizes.	Y/N		
-------------	---	-----	--	--

**Modification 3: At ANNEX A STATEMENT OF REQUIREMENT:**

**Delete:**

<b>A1.11</b>	Scanner must capable of scanning drawings up to 38" wide up to 900 dpi
--------------	--

**Insert:**

<b>A1.11</b>	Scanner must capable of scanning drawings up to a maximum of 38" wide with a minimum 600 dpi
--------------	--

**Modification 4: At ATTACHMENT 4.1 SUBSTANTIATION OF TECHNICAL COMPLIANCE FORM:**

**Delete:**

<b>A1.11</b>	Scanner must capable of scanning drawings up to 38" wide up to 900 dpi	Y/N		
--------------	--	-----	--	--

**Insert:**

<b>A1.11</b>	Scanner must capable of scanning drawings up to a maximum of 38" wide with a minimum 600 dpi	Y/N		
--------------	--	-----	--	--

**Modification 5: At ANNEX A STATEMENT OF REQUIREMENT:**

**Delete:**

<b>A1.12</b>	Scanner must be capable of scanning large drawings up to 42"x 72" from Color, B&W, Dark originals, Photo Maps, red line drawings, and older cad drawings.
--------------	---

**Insert:**

<b>A1.12</b>	Scanner must be capable of scanning large drawings up to 38"x 72" from Color, B&W, Dark originals, Photo Maps, red line drawings, and older cad drawings.
--------------	---

**Modification 6: At ATTACHMENT 4.1 SUBSTANTIATION OF TECHNICAL COMPLIANCE FORM:**

**Delete:**

<b>A1.12</b>	Scanner must be capable of scanning large drawings up to 42"x 72" from Color, B&W, Dark originals, Photo Maps, red line drawings, and older cad drawings.	Y/N		
--------------	---	-----	--	--

**Insert:**

<b>A1.12</b>	Scanner must be capable of scanning large drawings up to 38"x 72" from Color, B&W, Dark originals, Photo Maps, red line drawings, and older cad drawings.	Y/N		
--------------	---	-----	--	--

**ALL OTHER TERMS AND CONDITIONS OF THE REQUEST FOR PROPOSAL (RFP) REMAIN UNCHANGED.**