



## RETURN BIDS TO:

## RETOURNER LES SOUMISSIONS À:

Bid Receiving - PWGSC / Réception des soumissions -  
TPSGC

11 Laurier St. / 11, rue Laurier

Place du Portage, Phase III

Core 0B2 / Noyau 0B2

Gatineau, Québec K1A 0S5

Bid Fax: (819) 997-9776

## SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

### Comments - Commentaires

### Vendor/Firm Name and Address

Raison sociale et adresse du  
fournisseur/de l'entrepreneur

### Issuing Office - Bureau de distribution

Vehicles & Industrial Products Division

140 O'Connor, Tower East

4th Floor

140 O'Connor, Tour Est

4ème étage

Ottawa

Ontario

K1A 0S5

<b>Title - Sujet</b> Medium Trucks	
<b>Solicitation No. - N° de l'invitation</b> 46272-218762/A	<b>Amendment No. - N° modif.</b> 003
<b>Client Reference No. - N° de référence du client</b> 1000358762	<b>Date</b> 2022-01-07
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$\$\$HP-940-80612	
<b>File No. - N° de dossier</b> hp940.46272-218762	<b>CCC No./N° CCC - FMS No./N° VME</b>
<b>Solicitation Closes - L'invitation prend fin</b> <b>at - à 02:00 PM</b> Eastern Standard Time EST <b>on - le 2022-01-18</b> Heure Normale du l'Est HNE	
<b>F.O.B. - F.A.B.</b> <b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input checked="" type="checkbox"/> <b>Other-Autre:</b> <input type="checkbox"/>	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Murray, David	<b>Buyer Id - Id de l'acheteur</b> hp940
<b>Telephone No. - N° de téléphone</b> (613) 296-9230 ( )	<b>FAX No. - N° de FAX</b> ( ) -
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b> Specified Herein Précisé dans les présentes	

Instructions: See Herein

Instructions: Voir aux présentes

<b>Delivery Required - Livraison exigée</b>	<b>Delivery Offered - Livraison proposée</b>
<b>Vendor/Firm Name and Address</b> <b>Raison sociale et adresse du fournisseur/de l'entrepreneur</b>	
<b>Telephone No. - N° de téléphone</b> <b>Facsimile No. - N° de télécopieur</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm</b> <b>(type or print)</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/</b> <b>de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b>	
<b>Signature</b>	<b>Date</b>

Solicitation No. - N° de l'invitation  
46272-218762/A

Amd. No. - N° de la modif.  
003

Buyer ID - Id de l'acheteur  
HP940

Client Ref. No. - N° de réf. du client

File No. - N° du dossier  
Hp940. 46272-218762/A

CCC No./N° CCC - FMS No/ N° VME

---

This Solicitation Amendment 003 is raised to extend the solicitation closing date and address bidders questions.

The solicitation closing date is hereby extended as followed:

Current closing date: 2022-01-14 at 02:00 PM Eastern Standard Time

New closing date: 2022-01-18 at 02:00 PM Eastern Standard Time

**Question 1:**

Item 1, Feature # 24 requests 11R tires. In the Industry, trucks of this size (19000 lb GVWR feature # 3) standardize on 19.5" tires. Can this be changed?

**Answer:**

Yes, refer to the attached revised specifications.

**Question 2:**

Item 2, Feature # 16 requests driver and passenger side air bags. In the Industry, air bags are not available on 3 ton vehicles (Feature # 1). Can this be deleted?

**Answer:**

Yes, refer to the attached revised specifications.

**Question 3:**

Item 2, Feature 32 requests an engine immobilizer. In the industry, this item is not available on 3 ton (Feature # 1) sized trucks. Can this be deleted?

**Answer:**

Yes, refer to the attached revised specifications.

Solicitation No. - N° de l'invitation  
46272-218762/A

Amd. No. - N° de la modif.  
003

Buyer ID - Id de l'acheteur  
HP940

Client Ref. No. - N° de réf. du client

File No. - N° du dossier  
Hp940. 46272-218762/A

CCC No./N° CCC - FMS No/ N° VME

---

**Delete:**

Annex "A" - Specifications - Medium Truck (Item 001)

Annex "B" - Specifications - Medium Truck (Item 002)

**Insert:**

Annex "A" - Specifications - Medium Truck (Item 001) Revision 001 attached herein

Annex "B" - Specifications - Medium Truck (Item 002) Revision 001 attached herein

---

ALL OTHER TERMS AND CONDITIONS REMAIN THE SAME

## Annex "A" - Specifications - Medium Truck (Item 001) Revision 001

PROPOSALS WILL BE EVALUATED IN ACCORDANCE WITH THE MANDATORY EVALUATION CRITERIA DETAILED BELOW.

Indicate the proposed make and model:

MAKE: \_\_\_\_\_

MODEL: \_\_\_\_\_

Bidders must indicate compliance to the following mandatory requirements by checking "yes" or "no". If additional information is submitted, the page number should be provided.

Feature #	MANDATORY REQUIREMENTS FOR THE TRUCK	Compliant:		Page Reference
		Yes	No	
1	Medium Truck, 2022 or Newer, Cube Van.			
2	Conventional, Regular Cab and Chassis.			
3	GVWR of 8,600 kg (19,000 lbs) minimum.			
4	Minimum Payload, 6000 lbs.			
5	Cab to Axle: To accommodate length of body specified.			
6	Automatic transmission.			
7	Drivetrain: 4 x 2			
8	Front Row Seating for three people.			
9	Back-up alarm.			
10	Block heater.			
11	Mud flaps Mounted behind front and rear wheels.			
12	Air conditioning for the cab.			
13	Manufacturer's AM/FM radio with Bluetooth hand free assist.			
14	Heated Power Mirrors.			
15	Power Windows.			
16	Cruise Control.			
17	90+ Amp Alternator Minimum.			
18	2 <sup>nd</sup> battery for Electric Hydraulic Tailgate.			
19	Gas Engine, Minimum 350HP			
20	Backup camera.			
21	Colour: white			
22	Weight Slip of Completed Vehicle Including Box and Equipment Must be Provided at Delivery.			
23	Minimum 130 Liter Capacity Fuel Tank.			
24	19.5" Tires, Mud and Snow Rear			
25	Driver and Passenger Side Air Bags.			
26	Standard Horn.			
27	Intermittent Wipers.			
28	Differential / Limited Slip.			
29	Brakes Hydraulic.			
30	Power Assisted Steering.			
31	Voltmeter or Battery warning light , temperature and oil pressure gauges.			
32	Dual Sun Visors.			
33	Dual Rear Wheels.			
34	Full Sized Spare Tire on Rim.			
35	Vinyl or Rubber floor mats.			
Feature #	MANDATORY REQUIREMENTS FOR THE BOX	Yes	No	Page Reference
36	Heavy Duty Van Body Type Aluminum Box - White Minimum .040 ga aluminum			
37	Exterior Length 16 feet / Exterior Minimum Width 96 inches / Interior Minimum Height 92 inches.			
38	Body to be finished in Plywood Inside ½" (in) Plywood Lining on side walls and ¾" (in) on front walls.			
39	Roll-up door c/w side-seals with 88" (in) high and 85 1/2" (in) wide opening – minimum Provided with a heavy duty lever lock with provision for locking with a padlock.			
40	3 Rows of Tie Bars, Kinedyne System E Series on side walls & front wall, in order to properly secure loads: 16", 36" and 60" from the floor.			
41	1 3/8" Ship Lap Hardwood Floor on 12" (in) centre.			
42	LED Brake and Reverse Lights Mounted on Exterior of Box.			

43	Kick Plate on Sides and Front Wall 12GA 12" High.			
44	LED Spot Lamp at Middle Interior of Box with Timer. Switch at Top Right Rear Corner.			
45	One Pair Non-metallic Grab Handles on Door Pillars.			
46	Box Mounted License Plate and Lights.			
47	Full Length translucent roof.			
48	One-piece roof with 2" top-hat roof bows – or equivalent.			
49	Aluminum extrusion aide posts on 12" (in) centres – or equivalent.			
50	Aluminum extrusion bottom rail with built in rub rail – or equivalent.			
51	3" (in) structural channel cross members with 5" (in) structural channel longsills – or equivalent.			
52	Recessed 3/16" (in) steel checkerplate threshold at 48" (in) deep.			
53	Splash Shields – or equivalent.			
Feature #	<b>MANDATORY REQUIREMENTS FOR THE LIFT GATE</b>	Yes	No	Page Reference
54	Aluminum Stowaway Liftgate.			
55	Aluminum Platform Size 80"x 48" Minimum.			
56	Lifting Capacities 3500 lbs Minimum.			
57	Full Taper Ramp.			
58	Gravity Down or Power Down, Self-leveling, Dual or Single Hydraulic Cylinder.			
59	Military Spec Toggle Switch Control.			
60	Dual Automatic Safety Latches Lock Platform in Stored Position.			
61	Electric Hydraulic, Heavy-Duty 12 volt DC Motor with Enclosure.			
62	Includes 150 amp Circuit Breaker.			
63	Heavy Duty Dock Bumpers approx. 3" (in) depth.			
64	Side Steps on Passenger Side for Access to the Box.			

The following is an example of the Liftgate:



## Annex "B" - Specifications - Medium Truck (Item 002) Revision 001

PROPOSALS WILL BE EVALUATED IN ACCORDANCE WITH THE MANDATORY EVALUATION CRITERIA DETAILED BELOW.

Indicate the proposed make and model:

MAKE: \_\_\_\_\_

MODEL: \_\_\_\_\_

Bidders must indicate compliance to the following mandatory requirements by checking "yes" or "no". If additional information is submitted, the page number should be provided.

		Compliant:		
Feature #	MANDATORY REQUIREMENTS FOR THE TRUCK	Yes	No	Page Reference
1	Medium Truck, 2022 or Newer, 3 Ton Cube Van Rear Axle Model.			
2	Conventional, Regular Cab and Chassis.			
3	GVWR must have the capacity to carry a Minimum Payload of 12,000 lbs (4 skids at approx. 3,000 lbs each).			
4	Cab to Axle Dimension to Accommodate 12 (ft) box.			
5	Box height must line up with loading dock, loading dock floor is 4 feet from ground.			
6	Diesel Engine, Minimum 320 HP.			
7	Minimum Capacity Fuel Tank (50 gallons).			
8	Automatic transmission.			
9	Air conditioning for the Cab.			
10	Frame with Minimum RBM (479,000 RBM).			
11	Rust Proof Undercoating.			
12	Block Heater.			
13	11R tires, Mud and Snow Rear.			
14	Heated Power Mirrors.			
15	Seats – Driver and Passenger (separate).			
16	Air Seat – Driver's side.			
17	Air Suspension.			
18	Air Horn for Highway Driving.			
19	Cruise Control.			
20	Intermittent Wipers.			
21	Manufacturer's AM/FM radio with Bluetooth Hand Free Assist.			
22	Hydraulic Brakes.			
23	Starting Aids for Diesel Engine.			
24	Power assisted steering.			
25	Voltmeter or Battery warning light , temperature and oil pressure gauges.			
26	Dual Sun Visors.			
27	Dual Rear Wheels.			
28	Full Sized Spare Tire on Rim.			
29	Backup Alarm.			
30	Backup Camera.			
31	Vinyl or Rubber floor mats.			
32	Colour: White			
Feature #	MANDATORY REQUIREMENTS FOR THE BOX	Yes	No	Page Reference
33	Heavy Duty Van Body Type Aluminum Box.			
34	Minimum Exterior Length 12 feet / Minimum Exterior Width - 102 inches / Exterior Minimum Height - 104 inches.			
35	Roll-up door side-seals with 96" (in) high and 91" (in) wide opening – minimum (The height must be measured from the floor to the retracted roll-up door) Provided with a heavy duty lever lock with provision for locking with a padlock.			
36	Minimum Gauge steel rear door frame (20 gauge).			
37	Full Length Translucent Roof.			
38	One-piece Roof with 2" Top-Hat Roof Bows – or equivalent.			
39	Aluminum Extrusion Aide Posts on 12" (in) Centres – or equivalent.			
40	Aluminum extrusion bottom rail with built in rub rail – or equivalent.			
41	3" (in) Structural Channel Cross Members with 5" (in) Structural Channel Longsills – or equivalent.			
42	½" (in) Plywood Lining on Side Walls and ¾" (in) on Front Walls.			
43	18" (in) Galvanized Extruded Scuffplate on Walls and Front.			
44	Recessed 3/16" (in) Steel Checkerplate Threshold at 48" (in) Deep.			
45	1 3/8" Ship Lap Hardwood Floor on 12" (in) Centre.			
46	Two 6,000 lbs Rated Heavy Duty Cargo Lockdown Anchors in Floor.			
47	Two Rows of Cargo Control on Side and Front Walls, one at 30" (in) Centres and one at 60" (in) Centres from the Floor.			
48	Interior Door Lights with Pilot Light in Cab.			

49	One Pair Non-metallic Grab Handles on Door Pillars.			
50	All required Body Clearance Lights and Reflectors.			
51	Splash Shields – or equivalent.			
52	Pre-painted White Panels .040 ga aluminum – or equivalent.			
53	Undercoated Underbody.			
54	Mud Flaps Mounted behind the Rear Axle and Front Tires.			
<b>Feature #</b>	<b>MANDATORY REQUIREMENTS FOR THE LIFT GATE</b>	<b>Yes</b>	<b>No</b>	<b>Page Reference</b>
55	Fold and Stow style – Level ride.			
56	Capacity – 3,000 lbs – Minimum.			
57	Aluminum 60" X 80" – Minimum.			
58	Cart Stop.			
59	Steel Pump and Motor Enclosure – or equivalent.			
60	Heavy Duty Dock Bumpers approx. 3" (in) depth.			
61	Side Steps on Passenger Side for Access to the Box.			
62	Dual Hydraulics.			