



**RETURN BIDS TO:**

**RETOURNER LES SOUMISSIONS À:**

Bid Receiving Public Works and Government  
Services Canada/Réception des soumissions/Travaux  
publics et Services gouvernementaux Canada  
See herein for bid submission  
instructions/

Voir la présente pour les  
instructions sur la présentation  
d'une soumission

NA  
Ontario

**SOLICITATION AMENDMENT  
MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise  
indicated, all other terms and conditions of the Solicitation  
remain the same.

Ce document est par la présente révisé; sauf indication contraire,  
les modalités de l'invitation demeurent les mêmes.

**Comments - Commentaires**

**Vendor/Firm Name and Address**  
**Raison sociale et adresse du**  
**fournisseur/de l'entrepreneur**

**Issuing Office - Bureau de distribution**  
Public Works and Government Services / Travaux  
publics et services gouvernementaux  
Kingston Procurement  
Des Acquisitions Kingston  
86 Clarence Street, 2nd floor  
Kingston  
Ontario  
K7L 1X3

<b>Title - Sujet</b> High Speed Camera	
<b>Solicitation No. - N° de l'invitation</b> W6448-22C019/A	<b>Amendment No. - N° modif.</b> 002
<b>Client Reference No. - N° de référence du client</b> W6448-22C019	<b>Date</b> 2022-02-01
<b>GETS Reference No. - N° de référence de SEAG</b> PW-\$KIN-555-8577	
<b>File No. - N° de dossier</b> KIN-1-56142 (555)	<b>CCC No./N° CCC - FMS No./N° VME</b>
<b>Solicitation Closes - L'invitation prend fin</b> <b>at - à 02:00 PM</b> Eastern Standard Time EST <b>on - le 2022-02-09</b> Heure Normale du l'Est HNE	
<b>F.O.B. - F.A.B.</b> Specified Herein - Précisé dans les présentes <b>Plant-Usine:</b> <input type="checkbox"/> <b>Destination:</b> <input type="checkbox"/> <b>Other-Autre:</b> <input checked="" type="checkbox"/>	
<b>Address Enquiries to: - Adresser toutes questions à:</b> Webster, Sean	<b>Buyer Id - Id de l'acheteur</b> kin555
<b>Telephone No. - N° de téléphone</b> (873) 354-9545 ( )	<b>FAX No. - N° de FAX</b> (613) 545-8067
<b>Destination - of Goods, Services, and Construction:</b> <b>Destination - des biens, services et construction:</b>	

**Instructions: See Herein**

**Instructions: Voir aux présentes**

<b>Delivery Required - Livraison exigée</b>	<b>Delivery Offered - Livraison proposée</b>
<b>Vendor/Firm Name and Address</b> <b>Raison sociale et adresse du fournisseur/de l'entrepreneur</b>	
<b>Telephone No. - N° de téléphone</b> <b>Facsimile No. - N° de télécopieur</b>	
<b>Name and title of person authorized to sign on behalf of Vendor/Firm</b> <b>(type or print)</b> <b>Nom et titre de la personne autorisée à signer au nom du fournisseur/</b> <b>de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b>	
<b>Signature</b>	<b>Date</b>

---

**Amendment 002** – High Speed Camera is being issued to respond to suppliers' questions.

---

**REFERENCE: Annex A, Section 4.3 Weight/Size:**

**Q1:** Would the end user accept a high-speed camera with a weight of 9.1Kg instead of 7Kg ?

**A1:** Yes, a maximum weight of 10kg will be accepted.

**Q2:** What if the dimensions were 7x7.4x11.7 inches instead of 6x6x12 inches ?

**A2:** Yes, dimensions of up to 8x8x14 inches will be accepted.

**DELETE:**

"Have a maximum body size (excluding protrusions) as follows:

- a. Length: a maximum of 30.48 cm (12 in);
- b. Width: a maximum of 15.24 cm (6 in);
- c. Height: a maximum of 15.24 cm (6 in); and
- d. Have a weight (including batteries) of no more than 7 kg (15.4 pounds)."

**INSERT:**

"Have a maximum body size (excluding protrusions) as follows:

- a. Length: a maximum of 14 in;
- b. Width: a maximum of 8 in;
- c. Height: a maximum of 8 in; and
- d. Have a weight (including batteries) of no more than 10 kg.

---

**REFERENCE: Section 4.1.1.1 MTC 4 – Resolution**

**Q3:** For MTC4, would 50000 fps at 1280x800 be sufficient?

**A3:** Yes.

**DELETE:** "a. Have a minimum resolution of 1024 x 1024 at a frame rate of 12,000 frames per second (fps);"

**INSERT:** "a. Have a minimum resolution of 1024 x 1024 or 1280 x 800 at a minimum frame rate of 12,000 frames per second (fps);"

**REFERENCE: Annex A Section 5.3 – Resolution**

**DELETE:** "a. Have a minimum resolution of 1024 x 1024 at a frame rate of 12,000 frames per second (fps);"

**INSERT:** "a. Have a minimum resolution of 1024 x 1024 or 1280 x 800 at a minimum frame rate of 12,000 frames per second (fps);"

---

Solicitation No. - N° de l'invitation  
W6448-22C019/C  
Client Ref. No. - N° de réf. du client  
W6448-22-C019

Amd. No. - N° de la modif.  
002  
File No. - N° du dossier  
KIN-1-56142

Buyer ID - Id de l'acheteur  
KIN555  
CCC No./N° CCC - FMS No./N° VME

---

**REFERENCE: Section 4.1.1.1 MTC 2 – Power Requirements**

**Q4:** Will the end user accept a DC voltage range of 22-32 V instead of 18-36 V ?

**A4:** Yes, as long as the DC converter can be connected to a 110 V outlet.

**DELETE:** "ii. DC Voltage: 18-36 VDC"

**INSERT:**

"ii. Minimum DC Voltage range of 22-32 VDC, and must capable of being to connected to a 110V outlet through a DC Converter."

**REFERENCE: Annex A Section 4.4**

**DELETE:** "ii. DC Voltage: 18-36 VDC"

**INSERT:**

"ii. Minimum DC Voltage range of 22-32 VDC, and must capable of being to connected to a 110V outlet through a DC Converter."

---

**ALL OTHER TERMS AND CONDITIONS REMAIN UNCHANGED**