



RETURN BIDS TO:

RETOURNER LES SOUMISSIONS À:

Bid Receiving - PWGSC / Réception des soumissions -
TPSGC

11 Laurier St. / 11, rue Laurier

Place du Portage, Phase III

Core 0B2 / Noyau 0B2

Gatineau, Québec K1A 0S5

Bid Fax: (819) 997-9776

SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address

Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution

Vehicles & Industrial Products Division

140 O'Connor, Tower East

4th Floor

140 O'Connor, Tour Est

4ème étage

Ottawa

Ontario

K1A 0S5

Title - Sujet Medium Trucks	
Solicitation No. - N° de l'invitation 46272-218762/C	Amendment No. - N° modif. 001
Client Reference No. - N° de référence du client 1000358762	Date 2022-03-16
GETS Reference No. - N° de référence de SEAG PW-\$\$\$HP-940-81044	
File No. - N° de dossier hp940.46272-218762	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM Eastern Daylight Saving Time EDT on - le 2022-04-04 Heure Avancée de l'Est HAE	
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Murray, David	Buyer Id - Id de l'acheteur hp940
Telephone No. - N° de téléphone (613) 296-9230 ()	FAX No. - N° de FAX () -
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Solicitation No. - N° de l'invitation
46272-218762/C

Amd. No. - N° de la modif.
001

Buyer ID - Id de l'acheteur
HP940

Client Ref. No. - N° de réf. du client

File No. - N° du dossier
Hp940. 46272-218762/C

CCC No./N° CCC - FMS No/ N° VME

This Solicitation Amendment 001 is raised to address bidders questions.

Question #1:

The only tires available are LT 225/70R 19.5". Can this be changed?

Response:

Yes, refer to the attached revised specifications.

Question 2:

Please clarify the payload for item 002 – Specification #4.

Response:

"Payload" refers to the total weight of goods, materiel and/or passengers carried in a typical load.
Please refer to the attached revised specifications, both items require the same payload.

Delete:

Annex "A" - Specifications - Medium Truck (Item 001)
Annex "B" - Specifications - Medium Truck (Item 002)

Insert:

Annex "A" - Specifications - Medium Truck (Item 001) Revision 001 attached herein.
Annex "B" - Specifications - Medium Truck (Item 002) Revision 001 attached herein.

ALL OTHER TERMS AND CONDITIONS REMAIN THE SAME

Annex “A” - Specifications - Medium Truck (Item 001) Revision 001

PROPOSALS WILL BE EVALUATED IN ACCORDANCE WITH THE MANDATORY EVALUATION CRITERIA DETAILED BELOW.

Indicate the proposed make and model:

MAKE: _____

MODEL: _____

Bidders must indicate compliance to the following mandatory requirements by checking "yes" or "no". If additional information is submitted, the page number should be provided.

Feature #	MANDATORY REQUIREMENTS FOR THE TRUCK	Compliant:		Page Reference
		Yes	No	
1	Medium Truck, 2022 or Newer, Cube Van.			
2	Conventional, Regular Cab and Chassis.			
3	GVWR of 8,600 kg (19,000 lbs) minimum.			
4	Minimum Payload, 12000 lbs.			
5	Cab to Axle: To accommodate length of body specified.			
6	Automatic transmission.			
7	Drivetrain: 4 x 2			
8	Front Row Seating for three people.			
9	Back-up alarm.			
10	Block heater.			
11	Mud flaps Mounted behind front and rear wheels.			
12	Air conditioning for the cab.			
13	Manufacturer's AM/FM radio with Bluetooth hand free assist.			
14	Heated Power Mirrors.			
15	Power Windows.			
16	Cruise Control.			
17	90+ Amp Alternator Minimum.			
18	2 nd battery for Electric Hydraulic Tailgate.			
19	Gas Engine, Minimum 350HP			
20	Backup camera.			
21	Colour: white			
22	Weight Slip of Completed Vehicle Including Box and Equipment Must be Provided at Delivery.			
23	Minimum 130 Liter Capacity Fuel Tank.			
24	19.5" tires, Mud and Snow rear tires			
25	Driver and Passenger Side Air Bags.			
26	Standard Horn.			
27	Intermittent Wipers.			
28	Differential / Limited Slip.			
29	Brakes Hydraulic.			
30	Power Assisted Steering.			
31	Voltmeter or Battery warning light , temperature and oil pressure gauges.			
32	Dual Sun Visors.			
33	Dual Rear Wheels.			
34	Full Sized Spare Tire on Rim.			
35	Vinyl or Rubber floor mats.			
Feature #	MANDATORY REQUIREMENTS FOR THE BOX	Yes	No	Page Reference
36	Heavy Duty Van Body Type Aluminum Box - White Minimum .040 ga aluminum			
37	Exterior Length 16 feet / Exterior Minimum Width 96 inches / Interior Minimum Height 92 inches.			
38	Body to be finished in Plywood Inside ½" (in) Plywood Lining on side walls and ¾" (in) on front walls.			
39	Roll-up door c/w side-seals with 88" (in) high and 85 1/2" (in) wide opening – minimum Provided with a heavy duty lever lock with provision for locking with a padlock.			

40	3 Rows of Tie Bars, Kinedyne System E Series on side walls & front wall, in order to properly secure loads: 16", 36" and 60" from the floor.			
41	1 3/8" Ship Lap Hardwood Floor on 12" (in) centre.			
42	LED Brake and Reverse Lights Mounted on Exterior of Box.			
43	Kick Plate on Sides and Front Wall 12GA 12" High.			
44	LED Spot Lamp at Middle Interior of Box with Timer. Switch at Top Right Rear Corner.			
45	One Pair Non-metallic Grab Handles on Door Pillars.			
46	Box Mounted License Plate and Lights.			
47	Full Length translucent roof.			
48	One-piece roof with 2" top-hat roof bows – or equivalent.			
49	Aluminum extrusion aide posts on 12" (in) centres – or equivalent.			
50	Aluminum extrusion bottom rail with built in rub rail – or equivalent.			
51	3" (in) structural channel cross members with 5" (in) structural channel longills – or equivalent.			
52	Recessed 3/16" (in) steel checkerplate threshold at 48" (in) deep.			
53	Splash Shields – or equivalent.			
Feature #	MANDATORY REQUIREMENTS FOR THE LIFT GATE	Yes	No	Page Reference
54	Aluminum Stowaway Liftgate.			
55	Aluminum Platform Size 80"x 48" Minimum.			
56	Lifting Capacities 3500 lbs Minimum.			
57	Full Taper Ramp.			
58	Gravity Down or Power Down, Self-leveling, Dual or Single Hydraulic Cylinder.			
59	Military Spec Toggle Switch Control.			
60	Dual Automatic Safety Latches Lock Platform in Stored Position.			
61	Electric Hydraulic, Heavy-Duty 12 volt DC Motor with Enclosure.			
62	Includes 150 amp Circuit Breaker.			
63	Heavy Duty Dock Bumpers approx. 3" (in) depth.			
64	Side Steps on Passenger Side for Access to the Box.			

The following is an example of the Liftgate:



Annex “B” - Specifications - Medium Truck (Item 002) Revision 001

PROPOSALS WILL BE EVALUATED IN ACCORDANCE WITH THE MANDATORY EVALUATION CRITERIA DETAILED BELOW.

Indicate the proposed make and model:

MAKE: _____

MODEL: _____

Bidders must indicate compliance to the following mandatory requirements by checking “yes” or “no”. If additional information is submitted, the page number should be provided.

Feature #	MANDATORY REQUIREMENTS FOR THE TRUCK	Compliant:		Page Reference
		Yes	No	
1	Medium Truck, 2022 or Newer, Cube Van.			
2	Conventional, Regular Cab and Chassis.			
3	GVWR of 8,600 kg (19,000 lbs) minimum (Max. weight of 30,000 lbs)			
4	Minimum Payload, 12000 lbs.			
5	Cab to Axle: To accommodate length of body specified.			
6	Automatic transmission.			
7	Drivetrain: 4 x 2			
8	Front Row Seating for three people.			
9	Back-up alarm.			
10	Block heater.			
11	Mud flaps Mounted behind front and rear wheels.			
12	Air conditioning for the cab.			
13	Manufacturer's AM/FM radio with Bluetooth hand free assist.			
14	Heated Power Mirrors.			
15	Power Windows.			
16	Cruise Control.			
17	90+ Amp Alternator Minimum.			
18	2 nd battery for Electric Hydraulic Tailgate.			
19	Gas Engine, Minimum 350HP			
20	Backup camera.			
21	Colour: white			
22	Weight Slip of Completed Vehicle Including Box and Equipment Must be Provided at Delivery.			
23	Minimum 130 Liter Capacity Fuel Tank.			
24	19.5" tires, Mud and Snow rear tires			
25	Driver and Passenger Side Air Bags.			
26	Standard Horn.			
27	Intermittent Wipers.			
28	Differential / Limited Slip.			
29	Brakes Hydraulic.			
30	Power Assisted Steering.			
31	Voltmeter or Battery warning light , temperature and oil pressure gauges.			
32	Dual Sun Visors.			
33	Dual Rear Wheels.			
34	Full Sized Spare Tire on Rim.			
35	Vinyl or Rubber floor mats.			
Feature #	MANDATORY REQUIREMENTS FOR THE BOX	Yes	No	Page Reference
36	Heavy Duty Van Body Type Aluminum Box - White Minimum .040 ga aluminum			
37	Exterior Length 16 feet / Exterior Minimum Width 96 inches / Interior Minimum Height 92 inches.			
38	Body to be finished in Plywood Inside ½" (in) Plywood Lining on side walls and ¾" (in) on front walls.			
39	Roll-up door c/w side-seals with 88" (in) high and 85 1/2" (in) wide opening – minimum Provided with a heavy duty lever lock with provision for locking with a padlock.			

40	3 Rows of Tie Bars, Kinedyne System E Series on side walls & front wall, in order to properly secure loads: 16", 36" and 60" from the floor.			
41	1 3/8" Ship Lap Hardwood Floor on 12" (in) centre.			
42	LED Brake and Reverse Lights Mounted on Exterior of Box.			
43	Kick Plate on Sides and Front Wall 12GA 12" High.			
44	LED Spot Lamp at Middle Interior of Box with Timer. Switch at Top Right Rear Corner.			
45	One Pair Non-metallic Grab Handles on Door Pillars.			
46	Box Mounted License Plate and Lights.			
47	Full Length translucent roof.			
48	One-piece roof with 2" top-hat roof bows – or equivalent.			
49	Aluminum extrusion aide posts on 12" (in) centres – or equivalent.			
50	Aluminum extrusion bottom rail with built in rub rail – or equivalent.			
51	3" (in) structural channel cross members with 5" (in) structural channel longsills – or equivalent.			
52	Recessed 3/16" (in) steel checkerplate threshold at 48" (in) deep.			
53	Splash Shields – or equivalent.			
Feature #	MANDATORY REQUIREMENTS FOR THE LIFT GATE	Yes	No	Page Reference
54	Aluminum Stowaway Liftgate.			
55	Aluminum Platform Size 80"x 48" Minimum.			
56	Lifting Capacities 3500 lbs Minimum.			
57	Full Taper Ramp.			
58	Gravity Down or Power Down, Self-leveling, Dual or Single Hydraulic Cylinder.			
59	Military Spec Toggle Switch Control.			
60	Dual Automatic Safety Latches Lock Platform in Stored Position.			
61	Electric Hydraulic, Heavy-Duty 12 volt DC Motor with Enclosure.			
62	Includes 150 amp Circuit Breaker.			
63	Heavy Duty Dock Bumpers approx. 3" (in) depth.			
64	Side Steps on Passenger Side for Access to the Box.			

The following is an example of the Liftgate:

