



**RETURN BIDS TO:  
RETOURNER LES SOUMISSIONS A:**

Bid Receiving/Réception des soumissions  
Joshua.knox@rcmp-grc.gc.ca

**SOLICITATION  
AMENDMENT**

**MODIFICATION DE  
L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments: - Commentaries :

THIS DOCUMENT CONTAINS A SECURITY  
REQUIREMENT

<b>Title – Sujet</b> Office Seating for Training Facility located in Regina, Saskatchewan		<b>Date</b> March 21st, 2022
<b>Solicitation No. – N° de l'invitation</b> 202203060/A		<b>Amendment No. – N° de la modification</b> 02
<b>Client Reference No. - No. De Référence du Client</b> 202203060/A		
<b>Solicitation Closes – L'invitation prend fin</b>		
<b>At / à :</b>	14:00	EST (Eastern Standard Time) HNE (heure normale de l'Est)
<b>On / le :</b>	March 29th, 2022	
<b>F.O.B. – F.A.B</b>	<b>GST – TPS</b>	<b>Duty – Droits</b>
<b>Destination of Goods and Services – Destinations des biens et services</b>		
<b>Instructions</b>		
<b>Address Inquiries to – Adresser toute demande de renseignements à</b>		
<b>Telephone No. – No. de téléphone</b>		<b>Facsimile No. – No. de télécopieur</b>

<b>Delivery Required – Livraison exigée</b>	<b>Delivery Offered – Livraison proposée</b>
<b>Vendor/Firm Name, Address and Representative – Raison sociale, adresse et représentant du fournisseur/de l'entrepreneur:</b>	
<b>Telephone No. – No. de téléphone</b>	<b>Facsimile No. – No. de télécopieur</b>
<b>Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) – Nom et titre de la personne autorisée à signer au nom du fournisseur/de l'entrepreneur (taper ou écrire en caractères d'imprimerie)</b>	
<b>Signature</b>	<b>Date</b>



This amendment is raised to address the following:

- To respond to questions received during the solicitation period; and
- To revise the solicitation accordingly, as applicable.

### **QUESTIONS AND ANSWERS**

Question 1: Chair A4, A5 , A6 and A8– Ergonomic Stools. Stool heights are listed as a range from 23-33". having a stool at this high height range, with adjustable seat and adjustable tilt, poses a high likelihood of a tipping hazard. Would the client accept a stool with fixed seat and fixed tilt? If not will the client accept a lower seat height range and if so what range is acceptable?

Answer 1: Adjustable seat depth and tilt can be omitted, tables A4, A5, A6 have been amended and A8 will be amended to delete this requirement.

Question 2: For Table A6: Task Stool S2.4 (x 12), is an upholstered seat acceptable instead of a mesh seat?

Answer 2: No. A mesh seat is specifically requested for this stool.



**SOLICITATION REVISIONS**

1) On page 30-31,

DELETE:

**Table A8: Task Stool S3.3**



<b>CHAIR TYPE</b>	<b>QTY: 2</b>
<input type="checkbox"/> Rotary Chair (up to 275 lbs) <input type="checkbox"/> Rotary Chair large occupant (up to 400 lbs) <input checked="" type="checkbox"/> Rotary Stool with backrest	

<b>IMPORTANT:</b>			
Canada may request additional information to confirm criteria prior to contract award within a time period specified by the Identified User (IU). Suppliers must provide products that are compliant to the selected “ <input checked="" type="checkbox"/> ” Requirement Choices			
Criteria <i>Instructions</i>	Requirement Choices		
<b>A</b> <b>Headrest</b> <i>choose only 1</i>	<input type="checkbox"/> Yes – Adjustable and Removable (if applicable, indicate type of adjustment in additional criteria below) <i>Recommended with Standard Back Height</i> <input checked="" type="checkbox"/> No		
<b>B</b> <b>Backrest Height</b> <i>choose only 1</i>	<input checked="" type="checkbox"/> Standard = height between 450 mm (17.7 in.) to 660 mm (26.0 in.) <input type="checkbox"/> High = height greater than 660 mm (26.0 in.) <input type="checkbox"/> No preference = minimum height of 450mm (17.0 in.)		
	<input checked="" type="checkbox"/> No preference (It is recommended to select “no preference” as profiles do not affect functionality of chair). <input type="checkbox"/> Other = _____		
<b>C</b> <b>Lumbar Support</b> <i>choose ALL that are acceptable</i>	<u>Adjustable</u> <input checked="" type="checkbox"/> Up/Down = min. 50 mm (2.0 in.) height adjustment between 150mm (5.9 in.) to 250 mm (9.8 in.) <input type="checkbox"/> Other = _____		
	<input type="checkbox"/> Fixed = between 150 mm (5.9 in.) to 250 mm (9.8 in.) above seat		
<b>D</b> <b>Armrests</b> <i>choose ALL that are acceptable</i>	<u>Adjustable</u> <input checked="" type="checkbox"/> Height adjustable = min. 63 mm (2.5 in.) adjustment between 176 mm (6.9 in.) to 289 mm (11.4 in.) <input checked="" type="checkbox"/> Width adjustable = within the range of 443 mm (17.0 in.) to 493 mm (19.4 in.) <input checked="" type="checkbox"/> Pivot adjustable = min. 20 degrees inward and min. 10 degrees outward		
	<input type="checkbox"/> Fixed = height range between 200 mm (7.9 in.) to 250 mm (9.8 in.)		
	<input type="checkbox"/> None (no arm rests)		
<b>E</b> <b>Seat Depth</b> <i>choose ALL that are acceptable</i>	<input checked="" type="checkbox"/> Adjustable = min. 50 mm (2.0 in.) adjustment within the range 420 mm (16.5 in.) to 460 mm (18.1 in.)		
	<input type="checkbox"/> Fixed <table border="0" style="margin-left: 20px;"> <tr> <td><input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)</td> </tr> <tr> <td><input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)</td> </tr> <tr> <td><input type="checkbox"/> Deep = greater than 460 mm (18.1 in.)</td> </tr> </table>	<input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)	<input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)
<input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)			
<input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)			
<input type="checkbox"/> Deep = greater than 460 mm (18.1 in.)			



<b>F</b>	<i>Seat Width</i>	<i>Refer to chair type above</i> <i>Rotary chairs and stools = min. width of 450 mm (17.7in.)</i> <i>Rotary Large Occupant models = min. width of 560 mm (22.0 in.)</i>	
<b>G</b>	<i>Seat Height</i>  <i>choose ALL that are acceptable</i>	<i>Rotary Chair</i>	<input type="checkbox"/> Adjustable <input type="checkbox"/> Standard = includes 417 mm (16.4 in.) or less to 512 mm (20.2in.) or more <input type="checkbox"/> Low = includes 376 mm (14.8 in.) to 439 mm (17.3 in.) <input type="checkbox"/> Other = _____ <input type="checkbox"/> Fixed = between 417 mm (16.4 in.) to 512 mm (20.2 in.)
		<i>Rotary Stool with backrest</i>	<input checked="" type="checkbox"/> Adjustable = includes range from 580 mm (23 in.) to 840 mm (33 in.) <input type="checkbox"/> Fixed = equal or greater than 670 mm (27.5 in)
<b>H</b>	<i>Tilt Mechanism</i>  <i>choose only 1</i>	<input checked="" type="checkbox"/> Tilt Mechanism <i>seat and backrest adjust together in a ratio that falls within <math>\geq 1:1</math> (includes both Synchro-Tilt and Unison Tilt)</i> <input type="checkbox"/> Tilt Independently <i>seat and backrest adjust independently of each other</i> <input type="checkbox"/> No preference	
<b>I</b>	<i>Seat and Backrest Locks</i>  <i>choose ALL that are acceptable</i>	<input type="checkbox"/> Setup Position = <i>chair locks or stops at one position with seat flat and backrest straight</i> <input checked="" type="checkbox"/> Multiple Positions = <i>chair locks or stops at multiple positions (including setup position)</i>	
<b>J</b>	<i>Casters</i>	<input type="checkbox"/> carpet <input checked="" type="checkbox"/> hard surface	
<b>L</b>	<i>Foot Ring</i>	<i>Standard with stool models only</i>	
	<i>Finishes (Upholstery / Non-Upholstery)</i>  <i>choose ALL that are acceptable</i>	Backrest	<input type="checkbox"/> Upholstery <input type="checkbox"/> Other = _____ <input checked="" type="checkbox"/> Breathable material (Mesh)
		Seat	<input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Other = _____ <input type="checkbox"/> Breathable material (Mesh)
	<i>Additional Criteria:</i>		



INSERT:  
**Table A8: Task Stool S3.3**



<b>CHAIR TYPE</b>	<b>QTY: 2</b>
<input type="checkbox"/> Rotary Chair (up to 275 lbs) <input type="checkbox"/> Rotary Chair large occupant (up to 400 lbs) <input checked="" type="checkbox"/> Rotary Stool with backrest	

**IMPORTANT:**

Canada may request additional information to confirm criteria prior to contract award within a time period specified by the Identified User (IU).  
Suppliers must provide products that are compliant to the selected "■" Requirement Choices

	Criteria <i>Instructions</i>	Requirement Choices	
<b>A</b>	<b>Headrest</b> <i>choose only 1</i>	<input type="checkbox"/> Yes – Adjustable and Removable (if applicable, indicate type of adjustment in additional criteria below) Recommended with Standard Back Height <input checked="" type="checkbox"/> No	
<b>B</b>	<b>Backrest Height</b> <i>choose only 1</i>	<input checked="" type="checkbox"/> Standard = height between 450 mm (17.7 in.) to 660 mm (26.0 in.) <input type="checkbox"/> High = height greater than 660 mm (26.0 in.) <input type="checkbox"/> No preference = minimum height of 450mm (17.0 in.)	
	<b>Backrest Profile</b> <i>choose only 1</i>	<input checked="" type="checkbox"/> No preference (It is recommended to select "no preference" as profiles do not affect functionality of chair). <input type="checkbox"/> Other = _____	
<b>C</b>	<b>Lumbar Support</b> <i>choose ALL that are acceptable</i>	<u>Adjustable</u> <input checked="" type="checkbox"/> Up/Down = min. 50 mm (2.0 in.) height adjustment between 150mm (5.9 in.) to 250 mm (9.8 in.) <input type="checkbox"/> Other = _____	
		<input type="checkbox"/> Fixed = between 150 mm (5.9 in.) to 250 mm (9.8 in.) above seat	
<b>D</b>	<b>Armrests</b> <i>choose ALL that are acceptable</i>	<u>Adjustable</u> <input checked="" type="checkbox"/> Height adjustable = min. 63 mm (2.5 in.) adjustment between 176 mm (6.9 in.) to 289 mm (11.4 in.) <input checked="" type="checkbox"/> Width adjustable = within the range of 443 mm (17.0 in.) to 493 mm (19.4 in.) <input checked="" type="checkbox"/> Pivot adjustable = min. 20 degrees inward and min. 10 degrees outward	
		<input type="checkbox"/> Fixed = height range between 200 mm (7.9 in.) to 250 mm (9.8 in.)	
		<input type="checkbox"/> None (no arm rests)	
<b>E</b>	<b>Seat Depth</b> <i>choose ALL that are acceptable</i>	<input type="checkbox"/> Adjustable = min. 50 mm (2.0 in.) adjustment within the range 420 mm (16.5 in.) to 460 mm (18.1 in.)	
		<input checked="" type="checkbox"/> Fixed <table border="0" style="display: inline-table; vertical-align: top; margin-left: 20px;"> <tr> <td><input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)</td> </tr> <tr> <td><input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)</td> </tr> <tr> <td><input type="checkbox"/> Deep = greater than 460 mm (18.1 in.)</td> </tr> </table>	<input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)
<input type="checkbox"/> Shallow = 380 mm (15.0 in.) to 420 mm (16.5 in.)			
<input type="checkbox"/> Medium = greater than 420 mm (16.5 in.) to 460 mm (18.1 in.)			
<input type="checkbox"/> Deep = greater than 460 mm (18.1 in.)			
<b>F</b>	<b>Seat Width</b>	<u>Refer to chair type above</u> Rotary chairs and stools = min. width of 450 mm (17.7in.) Rotary Large Occupant models = min. width of 560 mm (22.0 in.)	



<b>G</b>	<b>Seat Height</b> choose ALL that are acceptable	<b>Rotary Chair</b>	<input type="checkbox"/> Adjustable <input type="checkbox"/> Fixed = between 417 mm (16.4 in.) to 512 mm (20.2 in.)	<input type="checkbox"/> Standard = includes 417 mm (16.4 in.) or less to 512 mm (20.2 in.) or more <input type="checkbox"/> Low = includes 376 mm (14.8 in.) to 439 mm (17.3 in.) <input type="checkbox"/> Other = _____
		<b>Rotary Stool with backrest</b>	<input checked="" type="checkbox"/> Adjustable = includes range from 580 mm (23 in.) to 840 mm (33 in.) <input type="checkbox"/> Fixed = equal or greater than 670 mm (27.5 in)	
<b>H</b>	<b>Tilt Mechanism</b> choose only 1	<input type="checkbox"/> Tilt Mechanism seat and backrest adjust together in a ratio that falls within $\geq 1:1$ (includes both Synchro-Tilt and Unison Tilt) <input type="checkbox"/> Tilt Independently seat and backrest adjust independently of each other <input checked="" type="checkbox"/> No preference		
<b>I</b>	<b>Seat and Backrest Locks</b> choose ALL that are acceptable	<input type="checkbox"/> Setup Position = chair locks or stops at one position with seat flat and backrest straight <input checked="" type="checkbox"/> Multiple Positions = chair locks or stops at multiple positions (including setup position)		
<b>J</b>	<b>Casters</b>	<input type="checkbox"/> carpet <input checked="" type="checkbox"/> hard surface		
<b>L</b>	<b>Foot Ring</b>	Standard with stool models only		
	<b>Finishes (Upholstery / Non-Upholstery)</b> choose ALL that are acceptable	<b>Backrest</b>	<input type="checkbox"/> Upholstery <input checked="" type="checkbox"/> Breathable material (Mesh)	<input type="checkbox"/> Other = _____
		<b>Seat</b>	<input checked="" type="checkbox"/> Upholstery <input type="checkbox"/> Breathable material (Mesh)	<input type="checkbox"/> Other = _____
	<b>Additional Criteria:</b>			