



RETURN BIDS TO:
RETOURNER LES SOUMISSIONS À:
PWGSC/TPSGC Acquisitions Bid Receiving
Box/Boîte de Réception des Soumissions
Bid Receiving Box/Boîte de Récepti
1st Floor/1^{ère} étage, Suite 1212
100-1045 Main Street
Moncton
New Brunswick
E1C 1H1
Bid Fax: (506) 851-6759

SOLICITATION AMENDMENT MODIFICATION DE L'INVITATION

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address
Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution
Acquisitions NB/PEI (Moncton Office) – Bureau
d'acquisitions N.-B./Î.-P.-É. (Moncton)
1045 Main Street / 1045, rue Main
Moncton
New Bruns
E1C 1H1

Title - Sujet Office Furniture, Category 2, 3 & 5 Office Furniture, Category 2, 3 & 5	
Solicitation No. - N° de l'invitation G9292-230940/A	Amendment No. - N° modif. 001
Client Reference No. - N° de référence du client G9292-230940	Date 2022-06-02
GETS Reference No. - N° de référence de SEAG PW-\$MCT-045-6216	
File No. - N° de dossier MCT-2-45009 (045)	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM Atlantic Daylight Saving Time ADT on - le 2022-06-14 Heure Avancée de l'Atlantique HAA	
F.O.B. - F.A.B. Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: MacFarlane (MCT), Andrew	Buyer Id - Id de l'acheteur mct045
Telephone No. - N° de téléphone (782) 377-4248 ()	FAX No. - N° de FAX (506) 851-6759
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Solicitation Amendment No. 001

Title: Office Furniture, Category 2, 3 & 5

(1) This solicitation is hereby amended to provide the following questions and answers:

Q1: Product Category 2 (Page 9) Does the end user have a proposed layout where these electric tables are being installed. For example, is the overall workstation size 72" x 72"? In this case, the main surface could then be 70" x 29" with a return surface at 40"W x 23"D.

A1: This product will be used in various offices; however, we are prepared to accept +/- 1" on each surface for both table sizes. Therefore 30"W X 72"L can be 29W'-31W' X 71"L-73"L and 24"W X 36"L can be 23W"-25W" X 35"L-37"L. The measurements are defined as Depth-Width Diameter x Length. Height adjustable 23" to 48.7".

DEPTH-WIDTH-DIAMETER	LENGTH	HEIGHT	CONTROLS
24	36	23 to 48.7	Electric
30	72	23 to 48.7	Electric

Q2: Is the first surface actually 36"W x 24"D as several manufacturer's only start their surfaces at 46"W because of the width of the electric base.

A2: The measurement is 24"W x 36"L - The measurements are defined as Depth-Width Diameter x Length. Height adjustable 23" to 48.7".

DEPTH-WIDTH-DIAMETER	LENGTH	HEIGHT	CONTROLS
24	36	23 to 48.7	Electric
30	72	23 to 48.7	Electric

Q3: For the second worksurface, is 70"W x 29"D acceptable? Electric table surfaces are normally slightly smaller to eliminate any pinch points when raising or lower the surface.

A3: See A1

Q4: Product Category 3 (Page 9) The GOCUID code is for a lower that is 12"W x 20"D x 48" to 54"H. Does the end user want this unit to be approximately 66"H?

A4: Yes. Annex A- Technical Specifications dimensions up to 66in high

.2 Dimensions: *(Refer to article 2.3 Tolerances for additional information)*

- .1 Must be 457 mm (18 in.) or 508 mm (20 in.) deep.
- .2 Each individual locker must be between 305 mm (12 in.) and 457 mm (18 in.) wide
- .3 The total height of all height options must be within 1219 mm (48 in.) to 1676 mm (66 in.) high.

N° de l'invitation - Solicitation No.
G9292-230940/A
N° de réf. du client - Client Ref. No.
G9292-230940

N° de la modif - Amd. No.
001
File No. - N° du dossier
MCT-2-45009

Id de l'acheteur - Buyer ID
MCT045
N° CCC / CCC No./ N° VME - FMS

ID	PRODUCT	TYPE OF PRODUCT	FORMAT	FINISHES	
D20XHXS	Storage Lockers	Storage Locker	One High	Painted Metal	

Q5: Does the end user want 389 Single Locker units as they are also sold in Double and Triple units. These are much cheaper than Single Lockers.

A5: We do not want double or triple stacked if they are stacked high, but we are willing to accept up to 50% of the total quantity if they are stacked side by side

Q6: If the end user wants a 66"H locker will slightly shorter models be acceptable? (ie) 64.5"H as most manufacturers have standard heights.

A6: We are prepared to accept - 2" on the height of the locker as our Annex A Technical specifications allows for 48" – 66" High

Q7: Does the end user want digital locks? They are requesting two different types, "built in locking mechanism" and "keyless, electric lock".

A7: Electric locks that are built in and keyless. Electronic locks must be programmable (able to accommodate assigned and shared usage)

RFID activated locks are the preferred mechanism for lockers

Where RFID is not available and numeric pads are utilised, consider brail along with printed numbers

Q8: Can you confirm if the end user wants Items 1 and 2 assembled at their Regional Warehouse and they will then look after transferring these tables to their Saint John office?

A9: Items to be assembled at Regional Warehouse and we will transfer to the end location.

Q9: Concerning the tops from Category 2: does the end user require these tops to be in true dimensions (24"x36" & 30"x72") or with "gap pinch" (23"x34" & 29"x70")?

A9: We are prepared to accept +/- 1" on each surface for both table sizes. Therefore 30"W X 72"L can be 29W'-31W' X 71"L-73"L and 24"W X 36"L can be 23W"-25W" X 35"L-37"L. The measurements are defined as Depth-Width Diameter x Length. Height adjustable 23" to 48.7"

DEPTH-WIDTH-DIAMETER	LENGTH	HEIGHT	CONTROLS
24	36	23 to 48.7	Electric
30	72	23 to 48.7	Electric

(2) Reference: Step 3 - PSIB

To clarify, this procurement is set aside under the federal government's Procurement Strategy for Indigenous Business (PSIB) **ONLY**. This procurement is set aside from the international trade agreements under the provision each has for set-asides for small and

N° de l'invitation - Solicitation No.
G9292-230940/A
N° de réf. du client - Client Ref. No.
G9292-230940

N° de la modif - Amd. No.
001
File No. - N° du dossier
MCT-2-45009

Id de l'acheteur - Buyer ID
MCT045
N° CCC / CCC No./ N° VME - FMS

minority businesses. Further to Article 800 of the Canadian Free Trade Agreement (CFTA), CFTA does not apply to this procurement.

If your bid has already been forwarded and you wish to revise same, this revision should be sent either in a sealed envelope and mailed to the above address or by facsimile (506) 851-6759 and reach the undersigned before the appropriate closing date. The solicitation number and the closing date are to be shown on the outside of the sealed envelope or on the facsimile transmission.

All other terms and conditions of the solicitation document remain unchanged remain unchanged.

All enquiries concerning this amendment are to be forwarded to:

Name: Andrew MacFarlane
161 St. Peters Road,
2nd Floor Suite 204
Charlottetown, PE
C1A 5P7

Telephone No: (782) 377-4248

Facsimile No: (506) 851-6759

Email: andrew.macfarlane@pwgsc-tpsgc.gc.ca