

### C3 FIELD DEVICE RECORD

(Reference: Clause 6.1 6)

#### C6.1 FIELD DEVICE TESTING - LEGEND & NOTES

(Reference: Clauses 6.7.4.1.3, 6.7.4.1.4, 6.7.4.1.5, 6.7.4.3.1, 6.7.4.5.1, 6.7.8.1.1, 6.7.8.2.2, 6.7.8.2.4)

DEVICE	DESCRIPTION	MANUFACTURER	MODEL NO.
M	Manual Station		270-SPO
M2	Manual Station		
M3	Manual Station		
RHT	Rate of Rise Heat Detector		281A
RHT2	Rate of Rise Heat Detector		
RHT3	Rate of Rise Heat Detector		
HT	Fixed Temperature Heat Detector		7682
HT2	Fixed Temperature Heat Detector		
HT3	Fixed Temperature Heat Detector		
S	Smoke Detector		1400A
	Sensitivity Test Method:		
	Sensitivity Range:		
S2	Smoke Detector		C2W-BA
	Sensitivity Test Method:		
	Sensitivity Range:		
S3	Smoke Detector		
	Sensitivity Test Method:		
	Sensitivity Range:		
RI	Remote Indicator		
DS	Duct Smoke Detector		
SFD	Supporting Field Device - Monitor		
SFD2	Supporting Field Device - Monitor		
FD	Sprinkler Flow Switch		
SS	Sprinkler Supervisory Device		
PS	Sprinkler Pressure Device		
IM	Isolation Module		
B	Bell		439D-6AWC
B2	Bell		
H/V	Horn/Visual		
H/V2	Horn/Visual		
H	Horn		
H2	Horn		
V	Visual Signal Device		
V2	Visual Signal Device		
SP	Cone Type Speaker		
SP2	Cone Type Speaker		
HSP	Horn Type Speaker		
AD	Ancillary Device		
AD2	Ancillary Device		
ET	Emergency Telephone		
EOL	End of Line Resistor/Capacitor		
EOL2	End of Line Resistor/Capacitor		



BUILDING NAME:	RCMP Lynn Lake	
BUILDING ADDRESS:	Lynn Lake, MB	
DATE:	Friday, September 24, 2021	
TEST NG PERFORMED BY:		

Printed Name

Signature

**EXIT AND EMERGENCY LIGHTING TEST AND INSPECTION RECORD**

Legend: BP = Battery Pack, 1BP = BP w/ 1 Head, 2BP = BP w/ 2 Heads, CP = Combo Pack, RH1 = Single Remote Head, RH2 = Dual Remote Head, ES = Exit Sign

Location	Unit Type (See Legend)	Unit Primary Voltage (VAC)	Rated Unit Emergency Voltage (VDC)	Unit Size (Watts)	Requires Service damaged, poor light, battery condition	Operation Confirmed	Heads properly aligned	Exit direction indicators correct	Duration of Test Time (minutes)	Test Time Result ✓ = Pass, x=Fail	Remarks / Deficiencies / Corrective Action
CELL AREA COFFEE ROOM	1BP	120	12	360	x	x	✓		30	x	Batteries 12V 35Ah, D1
BY HALL	RH2						✓				
GARAGE	RH1						✓				
GARAGE	RH1						✓				
MECHANICAL ROOM	1BP	120	12	360	x	x	✓		30	x	Batteries 12V 35Ah, D1
GENERAL OFFICE	RH1						✓				
BY LUNCH ROOM	RH1						✓				
GARAGE 2	RH2						✓				
MAIN ENTRANCE	RH1						✓				