



RETURN BIDS TO:

RETOURNER LES SOUMISSIONS À:

Bid Receiving - PWGSC / Réception des soumissions -
TPSGC

11 Laurier St. / 11, rue Laurier

Place du Portage, Phase III

Core 0B2 / Noyau 0B2

Gatineau

Québec

K1A 0S5

Bid Fax: (819) 997-9776

**SOLICITATION AMENDMENT
MODIFICATION DE L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments - Commentaires

Vendor/Firm Name and Address

Raison sociale et adresse du
fournisseur/de l'entrepreneur

Issuing Office - Bureau de distribution

Ship Construction, Refit and Related
Services/Construction navale, Radoubs et services
connexes

11 Laurier St. / 11, rue Laurier

6C2, Place du Portage

Gatineau

Québec

K1A 0S5

Title - Sujet Aluminum Utility boat	
Solicitation No. - N° de l'invitation 23239-230967/A	Amendment No. - N° modif. 001
Client Reference No. - N° de référence du client 23239-230967	Date 2023-05-26
GETS Reference No. - N° de référence de SEAG PW-\$\$MC-009-29076	
File No. - N° de dossier 009mc.23239-230967	CCC No./N° CCC - FMS No./N° VME
Solicitation Closes - L'invitation prend fin at - à 02:00 PM Eastern Daylight Saving Time EDT on - le 2023-07-04 Heure Avancée de l'Est HAE	
F.O.B. - F.A.B.	
Plant-Usine: <input type="checkbox"/> Destination: <input checked="" type="checkbox"/> Other-Autre: <input type="checkbox"/>	
Address Enquiries to: - Adresser toutes questions à: Gagnon, Brianne	Buyer Id - Id de l'acheteur 009mc
Telephone No. - N° de téléphone (873) 355-4939 ()	FAX No. - N° de FAX () -
Destination - of Goods, Services, and Construction: Destination - des biens, services et construction:	

Instructions: See Herein

Instructions: Voir aux présentes

Delivery Required - Livraison exigée	Delivery Offered - Livraison proposée
Vendor/Firm Name and Address Raison sociale et adresse du fournisseur/de l'entrepreneur	
Telephone No. - N° de téléphone Facsimile No. - N° de télécopieur	
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) Nom et titre de la personne autorisée à signer au nom du fournisseur/ de l'entrepreneur (taper ou écrire en caractères d'imprimerie)	
Signature	Date

Solicitation No. - N° de la sollicitation
23239-230967/A
Client Ref. No. - N° de réf. du client
23239-230967/A

Amd. No. - N° de la modif.
001
File No. - N° du dossier
23239-230967/A

Buyer ID - Id de l'acheteur
CCC No./N° CCC - FMS No./N° VME

Solicitation Amendment

This amendment is raised to:

- 1) Add the Technical Statement of Work to the Solicitation

1) Add the Technical Statement of Work to the Solicitation

Please see attached document (Technical Statement of Work)

ALL OTHER TERMS AND CONDITIONS REMAIN UNCHANGED.

TSOR

16' (4.8768 m) Aluminum utility boats

Special requirements and conditions to be met are identified with an Asterix (*).

Background: Polar Continental Shelf Program (PCSP) is a national service delivery agency providing logistical support to researchers from Canadian government agencies, northern communities, independent, and university groups conducting scientific activities in Canada's Arctic. Services include charter air transportation, accommodation at the Resolute facility, loaning of field equipment and communications to remote sites. The Program is administered by NRCan's Lands and Minerals Sector.

General

- * Aluminium utility boats are becoming more essential when it comes to higher load ratings to carry unique scientific equipment where a rigid structure is required to mount the equipment to. Additionally, an open floor design offers more volume to move around in.
- * The boat must be able to navigate and negotiate lakes, rivers, river inlets, deep & shallow waters, open water close to shorelines and rocky shores.
- * Sea State number 0

Requirements:

- * Colour – Black, blue, grey, or white are all acceptable colour schemes.
- * Total length must be between 15' (4.572 m) to 16' (4.8768 m) long.
- * Width must be at least 72" (182.88 cm) wide.
- * Minimal chine width of 61" (154.94 cm).
- * The depth needs to be at least 27" (68.58 cm) high.
- * A four-stroke outboard engine of at least 25hp must be offered with purchase
- * Transom height must be at 20" (50.8 cm) maximum to allow the use of outboard from our inventory selection
- * Total weight no more than 600 lbs (272.15 kg) without the outboard.
- * A trailer with a transom saver, transom tie downs (2), carpeted load guides (2) and a spare wheel is required

Specifications:

- * Must be able to use a 30hp outboard engine.
- * The gas container must remain portable at all times and must contain at least 20L worth of fuel.
- * A carrying capacity of at least 800 lbs (362.87 kg).
- * Stainless steel eyes to tie down and/or affix to both at the bow and stern.

- * The bottom and hull thickness must be at least 0.60" (15.24 mm) thick and made of a marine grade alloy.
- * An aluminum transom is the ideal choice for durability and longevity as well as a self-draining shelf.
- * Must be able to seat two adults by way of folding seats.
- * Storage areas built into the deck and sidewalls for safety equipment.
- * The floor must be flat and cleared of obstructions.
 - o No center seating running across the deck.
 - o The floor must be covered in marine grade vinyl.
 - o The floor must be made of marine grade plywood or aluminium.
- * An electric bilge pump is necessary given the size of the boat and its sealed floor.
- * An emergency reboarding ladder

Warranty & Repair Service

- * Product must be warranted against defective materials and /or workmanship for the normal / expected lifetime of the product.
- * Bidder must provide a certified repair services. Services may be allocated to a certified 3rd party service provider recognised by the bidder. Certified meaning that – any warranty repairs will not affect the manufacturer’s craftsmanship / material warranty;
- * Provide repair services (*certified 3rd party acceptable*) for non-warranty work at a reasonable cost; and
- * Repair to be performed using genuine products parts and materials.

Contract Forecast

Anticipated procurement for two units