



Royal Canadian Gendarmerie royale
Mounted Police du Canada

**RETURN BIDS TO:
RETOURNER LES SOUMISSIONS A :**

Bid Receiving/Réception des soumissions

NWR_Procurement_Bids@rcmp-grc.gc.ca

**SOLICITATION
AMENDMENT**

**MODIFICATION DE
L'INVITATION**

The referenced document is hereby revised; unless otherwise indicated, all other terms and conditions of the Solicitation remain the same.

Ce document est par la présente révisé; sauf indication contraire, les modalités de l'invitation demeurent les mêmes.

Comments: - Commentaries :

Title – Sujet 3D FDM PRINTER & CLEANING APPARATUS, REGINA, SK		Date October 23, 2023
Solicitation No. – N° de l'invitation M5000-24-00970/A		Amendment No. – N° de la modification 001
Client Reference No. - No. De Référence du Client 202400970		
Solicitation Closes – L'invitation prend fin		
At / à :	2 :00 PM	Central Standard Time
On / le :	November 06, 2023	
F.O.B. – F.A.B	GST – TPS	Duty – Droits
Destination of Goods and Services – Destinations des biens et services		
Instructions		
Address Inquiries to – Adresser toute demande de renseignements à Vince.Millan@rcmp-grc.gc.ca		
Telephone No. – No. de téléphone 587-340-9715		Facsimile No. – No. de télécopieur
Delivery Required – Livraison exigée		Delivery Offered – Livraison proposée
Vendor/Firm Name, Address and Representative – Raison sociale, adresse et représentant du fournisseur/de l'entrepreneur:		
Telephone No. – No. de téléphone		Facsimile No. – No. de télécopieur
Name and title of person authorized to sign on behalf of Vendor/Firm (type or print) – Nom et titre de la personne autorisée à signer au nom du fournisseur/de l'entrepreneur (taper ou écrire en caractères d'imprimerie)		
Signature		Date



This amendment is raised to address the following:

- To respond to questions received during the solicitation period; and
- To revise the solicitation accordingly, as applicable.

QUESTIONS AND ANSWERS

Question 1: In the specs, you are asking about dual extruder so that you can print with 2 materials at a time (build & support material). Our 3D Printer offers multi-material printing (up to 8 materials, including support) but from a single extruder. If multi material capability is what you are interested in, will this be okay with you?

Answer 1: Having two heads printing at the same time is what we are looking for as it wouldn't need to switch over materials while printing (material and support). Not switching between materials would save time and the ability to have up to 8 different materials doesn't benefit us.

Question 2: Noise level of less than 46dB, ours runs at 60dB, is this acceptable?

Answer 2: The printer will be in an office area and minimal sound is a great asset.

SOLICITATION REVISIONS

1) On page 21, REQUIREMENTS/SPECIFICATIONS

DELETE:

Minimum Specifications	Description
System size/weight (Length x Width x Height) of the FDM 3D Printer	Less than or equal to 65 in x 35 in x 30 in, Less than or equal to 550 lbs.

INSERT:

Minimum Specifications	Description
Maximum system weight of the FDM 3D Printer	Less than or equal to 550 lbs.