



CHAIR BUILDER



	QTY: <u>55</u>
<input checked="" type="checkbox"/> Rotary Chair <input type="checkbox"/> Rotary Chair large occupant <input type="checkbox"/> Rotary Stool	

[Link to annex A technical spec from the furniture website](#)

	Criteria	Requirement Choices	
A	Headrest	<input checked="" type="checkbox"/> No <input type="checkbox"/> Yes <input type="checkbox"/> No preference	
B	Backrest Height	<input checked="" type="checkbox"/> Standard = height between 450mm (17.7 in.) to 660 mm (25.9 in.) <input type="checkbox"/> High = height greater than 660mm (26 in.) <input type="checkbox"/> No preference	
B	Backrest Style Preference(s)	<input checked="" type="checkbox"/> No preference	 <p>Note: style represents overall shape, but the design may vary.</p>
C	Lumbar Support	<input checked="" type="checkbox"/> Adjustable = min. 50mm (2 in.) adjustment between 150mm (5.9 in.) to 250mm (9.8 in.) for height	<input checked="" type="checkbox"/> Up/down <input type="checkbox"/> In/out <input type="checkbox"/> In/out & up/down
		<input type="checkbox"/> Fixed = between 150 mm (5.9 in.) to 250 mm (9.8 in.)	
		<input type="checkbox"/> No preference	
D	Armrests	<input checked="" type="checkbox"/> Adjustable	<input type="checkbox"/> height = HEIGHT: min. 63mm (2.5 in.) adjustment between 176mm (6.9 in.) to 289mm (11.4 in.) <input type="checkbox"/> height & width = WIDTH: min.75mm (3 in.) between 443mm (17 in.) to 493mm (19.4 in.) <input checked="" type="checkbox"/> height, width & pivot = PIVOT: min. 20 degrees inward and min. 10 degrees outward <input type="checkbox"/> pivot
		<input type="checkbox"/> Fixed = height range between 200 mm (7.9 in.) to 250 mm (9.8 in.)	
		<input type="checkbox"/> None (no Armrests)	
E	Seat Depth	<input checked="" type="checkbox"/> Adjustable = min. 50mm (2 in.) adjustment within the range 420mm (16.5 in.) to 460mm (18.1 in.)	
		<input type="checkbox"/> Fixed	<input type="checkbox"/> Shallow = 380mm (15 in.) to 420mm (16.5 in.) <input type="checkbox"/> Medium = greater than 420mm (16.5 in.) to 460mm (18.1 in.) <input type="checkbox"/> Deep = greater than 460mm (18.1 in.)
		<input type="checkbox"/> No preference	
F	Seat Width	Standard rotary chairs and stools have a minimum width of 450mm (17.7in.) Large Occupant models have a minimum width of 560mm (22 in.)	
G	Seat Height	<input checked="" type="checkbox"/> Adjustable	<input checked="" type="checkbox"/> Standard = includes 417mm (16.4 in.) or less to 512mm (20.2in.) or more <input type="checkbox"/> Low = includes 376mm (14.8 in.) to 439mm (17.3 in.)
		<input type="checkbox"/> Fixed = between 417mm (16.4 in.) to 512mm (20.2 in.)	
H	Tilt Mechanism	<input type="checkbox"/> Synchro tilt = seat and backrest tilt at the same time in a simultaneous movement, with the seat in a ratio greater than 1:1 <input type="checkbox"/> Unison tilt = Seat and backrest (including knee) tilt in unison, a ratio of 1:1 <input type="checkbox"/> Back tilt = Seat angle and back angle adjustment to be adjustable independently of each other <input checked="" type="checkbox"/> No preference	
		<input type="checkbox"/> Setup Position = seat is in the most horizontal position and the backrest in the most vertical position <input checked="" type="checkbox"/> Multiple Positions = includes the setup position and additional angles of seat and backrest <input type="checkbox"/> No preference	
J	Casters	<input checked="" type="checkbox"/> carpet = for carpeted/ soft floors	<input type="checkbox"/> hard surface = for hard surfaced floors
K	Foot Ring	Standard with stool models only	
L	Upholstery	Backrest	<input checked="" type="checkbox"/> Upholstery <input checked="" type="checkbox"/> Mesh <input type="checkbox"/> Other ___ Cleanable _____
		Seat	<input checked="" type="checkbox"/> Upholstery <input checked="" type="checkbox"/> Mesh <input type="checkbox"/> Other ___ Cleanable _____
		<input type="checkbox"/> No preference	

--	--	--