


Reader Rail Panels and Bases





Panels (painted/treated plywood)				Avail. For Ter	Avail. Trav.Ex
Type	Qty	Dimensions	Condition		
Panel	1	36" x 14"	Good- Black powder coated, screw holes on one side and scratched on one side	Yes	Yes
Panel	1	48" x 16"	Good- One side powder coated with graphics on one side (has screw holes)	Yes	Yes
Panel	1	48" x 12"	Good- Black powder coated on one side. Other side has vinyl and graphics with s	Yes	Yes
Panel	1	48" x 12"	Good- Screw holes on the one side. black powder coated on one side. Other side	Yes	Yes
Panel	1	48" x 16"	Okay - Screw holes on the one side. Other side has black powder coat. Sides hav	Yes	Yes
Panel	1	48" x 14"	Okay -black coated, screw holes on one side. Other side has vinyl, slightly scuffe	Yes	Yes
Panel	1	54" x 14"	Good- black powder coated, one side has screw holes. Other side has vinyl.	Yes	Yes
Panel	1	42" x 16"	Slight damage - one side plain with screw holes, other side is black powder coat	Yes	Yes
Panel	1	70" x 14"	Good- black powder coated, screw holes on one side. Vinyl on the other side.	Yes	Yes
Metal bases				Avail. For Ter	Avail. Trav.Ex
Type	Qty	Dimensions	Condition		
Base	4	48" W x 12" D x 36" H	Good - very heavy	yes	yes



TEMPORARY WALL SYSTEM - MILA WALL SERIES 100 COMPONENT INVENTORY: Note: Available for Temporary Enhancements onsite, not for travelling.

Meters	Inches	Quantity	Notes
Mila wall (Series 100) Sound wall			
1.0 x 2.5	39.37 x 98.42	1	Cannot take nails or fasteners due to sound wiring inside.
Mila wall (Series 840) Nailable wall			
1.0 x 2.5	39.37 x 98.42	2	Not compatible with Series 100 system
Mila wall (Series 100) Nailable wall			
1.0 x 2.5	39.37 x 98.42	57	Updated Winter 2022 (purchased 2 x 100 series lg. 1 x 100 series sm. 2 x 840 series lg)
0.5 x 2.5	19.69 x 98.42	19	Used to support larger walls every ~3 meters
Mila wall (Series 100) Door Wall			
1.0 x 2.5	39.37 x 98.42	2	Mila door: 28 ¼" wide x 80 ½" high (useable width accounting for door)
Mila wall (Series 100) Alarm wall			
1.0 x 2.5	39.37 x 98.5	1	Nailable
TOTAL WALLS		80	

MILA WALL PROFILES INVENTORY (Used for Connecting 2 or more walls together at various angles)

Component Number	Thumbnail	Quantity	Notes
4.106.003 3 wall connector profile		2	
4.111.003 Rotating angle profile 020/90-180		8	Rotating angle piece that is affixed to a 180o straight wall. Angle can range from 20-90 degrees.
4.112.003 Corner profile 90x180/180x290		7	
4.108.003 Corner profile 40x40/1x1350		10	Fixed angle

Technical Inventory

Item	Surmounts	W	QTY	Notes	Available for Temporary Enhancement	Available for Travelling Exhibition
Touchscreen Kiosks						
A/V Kiosks - NEW (22" ELO screens)			2	Updated to ne	Yes	Yes
A/V Kiosks - OLD (22" ELO screens - OLD)			2		Yes	No
Amplifiers						
Amplifier - Extron external amplifier mounted on AV system			1		Yes	No
Amplifier - Lepy LP202A Hi-Fi Stereo Power Amplifier			1		Yes	No
Audio Amplifier - Trulink 40W Classroom			1		Yes	No
Projectors/Projector Equipment						
Projector - Casino XJ-A155V			1	Belongs to IT	Yes	No
Projector - Ceiling mount steel bars for projectors			2		Yes	No
Projector - Epson PowerLite 1975W projector with mount			1		Yes	No
Projector - Epson PowerLite 2250U projector with mount			3		Yes	No
Projector - FAVI Rio LED Projector			1		Yes	No
Projector - LED H20			2		Yes	No
Projector - Optoma Projector with mount, cables, remote			2		Yes	No
Projector ceiling mounts			4		Yes	No
NP-PA703UL-412L NEC Projector with No 6,917.72 Zoom Lens			1		Yes	No
Elite Screens ZRM-135H-REAR	66.19" high		2	https://www.	Yes	No
Screens/Tripods	9' wide		3		Yes	No
Media Players						
media player - BrightSign HD1024 (newest model)			3	PEX has 1 in th	Yes	Yes
media player - BrightSign HD1023			1	PEX has 1 in th	Yes	Yes
media player - BrightSign HD120 (oldest model)			5	PEX has one in	Yes	No
media player - MediaWhiz Sprite Media players			9	good for	Yes	Yes
media player - TechnoVision THD002 interactive			2	output	Yes	No
media players - ViewStream 500 HD media players			3	Older	Yes	No
Digital View AV players			6	Older	Yes	No
Speakers						
JB speaker - Large white (old)			1		Yes	No
Speaker - large			1		Yes	No
Speaker cables			Many		Yes	Yes
speakers - Atlas Sound surface mount loud speakers			2		Yes	Yes
speakers - Bose			13	Small Bose spk	Yes	Yes
Speakers - white, large with wall mounts (old)			2		Yes	No
Screens						
TV - 22" Dell Screens	22"		2		Yes	No
TV - 32" monitors - landscape view			2	LCD Monitor	Yes	No
TV - 32" NEC E324 LCD TV flatscreen slim with stand & mounting, Serial no. 3X0013	17 1/2" x 22"		1	NEC E324	Yes	No
TV - 46" monitors - landscape view			2	LCD Monitor	Yes	No
TV - 46" monitors - portrait view			3	LCD Monitor	Yes	No
TV - 53" Aquos Sharp Liquid Crystal TV with mount, 120 V, 60 Hz, 150 W, serial no. 80 5/8" x 5" w			3	One used in P	Yes	Yes
TV - HP Touchsmart 7320 Base			1		Yes	Yes
TV - LG Smart TV, 55", 120Hz, Wifi certified, 55LS5700, serial no. 208RMFP4D587	49.7 (H) x		1		Yes	No
TV 32" flatscreen bulky with stand & mounting	32"		1	Panasonic TH	Yes	No
TV 60" Sharp PNE601			3		Yes	Yes
ELO 32" Touchscreen	32"		1		Yes	Yes
ELO 15" Touchscreen	15"		1	ET1519L	Yes	Yes
TV 46-80" Mounting Hardware	NA		3		Yes	Yes
TV power adaptors			many		Yes	Yes
TV VGA cables			many		Yes	Yes
TV wall mount			1		Yes	Yes
Misc Tech						
Digital photo frames - Andoer	16.09		6		Yes	Yes
DisplayPort to HDMI adapter - 4K			2		Yes	Yes
Motion detectors			5		Yes	Yes
Router - Wireless broadband router 2.4 GHz			1		No	No
Timers			several		Yes	Yes
Audio Wands			many		Yes	Yes
Trigger buttons with bulbs			34		Yes	Yes
Aluminum LED Light Box Frames	46 3/4" x 98"		4		Yes	Yes



Exhibit Display Cases (wall mounted)											
Type	Item	QTY	Total Size	Prep Room	Interior Measurements			Notes	Available for Temporary Enhanc	Available for Travelling Exhibition	
Exhibit Case - Gem 3W	Gaylord - Little gem w	1	7 3/4 H x 7 W x 5 3/4 D	x	6"W x 6"D x 4"H			T-screw security	Yes	No	
Exhibit Case - Gem 10W	Gaylord - Little gem w	3	12H x 18W x 8"D	x	10 1/4H x 17W x 6 1/4"D			T-screw security	Yes	No	
Exhibit Case - Gem 8W	Gaylord - Little gem w	3	16 W x 12"D x 16 H	x	14 1/4H x 14 1/4W x 11"D			T-screw security	Yes	No	
Exhibit Display Cases (standing)											
Name	Type	Quantity	Total Size (inc base)	Exterior Glass Size	Interior Display LxOxH	incl chambr	volume	Security type	Description	Available for Temporary Enhanc	Available for Travelling Exhibition
Small case	Zirta ZC-101	1	16 x 16 x 53	17" high	15.5" x 15.5" x 7.25"	x 15.5" x 9.	259213/1.5ft3	security screw	and painted	Yes	No
Small case	Zirta	1	16 x 16 x 48	12" high	15.59" x 15.59" x 11.67"	x 15.59" x 1.	388813/2.25ft3	security screw	and painted	Yes	No
medium case	Zirta	4	22 x 22 x 48	12" high	21.59" x 21.59" x 11.67"	x 21.59" x 1.	691213/4ft3	security screw	and painted	Yes	No
medium case	Zirta	3	24 x 24 x 54	18" high	21.59" x 21.59" x 17.67"	x 21.59" x 1.	1036813/6ft3	security screw	and painted	Yes	No
large case	Zirta	2	28 x 28 x 48	12" high	27.59" x 27.59" x 11.67"	x 27.59" x 1.	1080013/6.25ft3	security screw	and painted	Yes	No
only	Zone ZF-101 Version	3	32"x32"x84"	32"x32"x84"	31" x 31" x 76.5"	" x 31" x 76.	8601613/48ft3	disguised by	laminated glass,	Yes	No
only	Zone ZF-101 Version	2	32"x32"x84"	32"x32"x84"	31" x 31" x 76.5"	" x 31" x 76.	8601613/48ft3	disguised by	laminated glass,	Yes	No
only	Zone ZF-101 Version	6	32"x32"x84"	32"x32"x84"	30 3/4" x 30 3/4" x 74.331"	**Display di	8601613/48ft3	ssure fitted v	laminated glass,	Yes	No
Table top cases	ZT-101	2	48"x24"x30 1/4"	8"	46.75" x 23" x 7.5"	" x 23" x 9.5	921613/5.33ft	key	and painted	Yes	No
Exhibit Plinths											
Plinth - silver	Plinth (painted silver)	1	29 x 29 x 36					Fits inside Zone Case		No	No
Plinth - plexi	Plinth (clear acrylic)	1	29 x 30 x 29					Fits inside Zone Case		No	No

Zone Case Accessories				
Type	Qty	ble for Temporary Enhanc	Available for Travelling Exhibition	
ZM-101 26 Straight Union Kit	Zone	4	Yes	No
ZM-101 26 Corner Union Kit	Zone	2	Yes	No
ZM-101 26 Double Union Kit	Zone	1	Yes	No
ZM-101 26 Shelving Unit - 4 rods w/	Zone	6	Yes	No
Lighting Kit Assembly ZM-101 26 (A)	Zone	1	Yes	No

IMAGES



Mannequins

Item (images available upon request)	QTY	Size	Notes	Avail. For Temp Enhanc	Avail. Trav.Ex
Mannequin heads with wigs	1	Various		Yes	Yes
Mannequin small - white torso	1			Yes	Yes
Mannequin small - grey torso	1			Yes	Yes
Mannequin male - grey torso	3			Yes	Yes
Mannequin stands	7		Needs rust remover	Yes	Yes
Mannequin female - grey torso	1			Yes	Yes
Mannequin female - white torso	3			Yes	Yes
Mannequin bases	1 box			Yes	Yes
Mannequin heads and hardware	1 box			Yes	Yes